

A good price performance by skilled craftsmanship

ALP's skilled craftsmanship realizes a good price performance with Japanese High Quality.

One-action safety interlock lid


Simply slide the lock lever one action to close the lid securely.

Safety comes first

At the end of the cycle, the lid will not be released until temperature has reached safe prescribed levels.

Three operation modes as standard

In addition to "Sterilization" pattern, "Sterilization/Warming" and "Dissolving/Warming" patterns as standard. Possible for a liquid sterilization depending on the setting.



Operation panel


◆ Options



Floating sensor



Printer



Recorder



Rapid cooling fan

Suppresses odor while operation

Equipped with an exhaust cooling tank to turn it into water droplets not raising the humidity of the surrounding environment to suppress odors during processing. Ideal also for a room where some devices with vulnerable to humidity are located.

A wide variety of options (Refer to the page 16-18)

- *Floating sensor: Measures a load temperature
- *Printer: Prints the temperature and time on roll paper
- *Recorder: Profiles the temperature and time of multiple sensors
- *Rapid cooling fan: Shortens the temperature drop time with cooling fan

MODEL	CL-32L	CL-40S	CL-40M	CL-40L
Chamber size/volume	φ320×H660mm/62L	φ400×H470mm/72L	φ400×H660mm/97L	φ400×H820mm/117L
Outer dimension/weight	W550×D620×H990mm/71kg	W620×D720×H880mm/84kg	W620×D720×H1000mm/88kg	W620×D720×H1160mm/95kg
Temperature(Max. press.)	100°C-140°C(0.290MPa)	100°C-137°C(0.270MPa)		
Sterilization time	0 minutes- 48 hours 00 minutes			
Dissolving temp./time	40°C-99°C / 0 minutes- 48 hours 00 minutes			
Warming temp./time	40°C-60°C / 0 minutes- 48 hours 00 minutes			
Safety device	Lid interlock, Water lack prevention, Over temperature prevention, Over pressure prevention Sensor breakage detection, Memory backup, Leakage breaker, Pressure safety valve			
Power demand	AC220/230/240V, 11/11/12A	AC220/230/240V,18/19/20A		
Wire basket/quantity	φ300×300mm/2 pcs.	φ380×200mm/2 pcs.	φ380×300mm/2 pcs.	φ380×400mm/2 pcs.

- Please specify voltage when you order.
- Specifications subject to change without notice for improvement.